How To Identify Your Lewmar Hatch

Hatches Produced after October 1997 have information stamped in the acrylic which will identify them - please quote this when ordering spares.

	Hatch Range (Click on a range to see further details.)							
Identifying features	Superhatch	Rollstop	Trimline	Coastline & Transport	<u>Ocean</u>	Concept	<u>Low</u> <u>Profile</u>	Medium Profile
Production Dates	80 - 87	86 - 92	88 - 99	91 - 99	91 - now	94 - 00	98	99
Height above deck (mm)	50	39 - 42	21	21	40 - 43	19	25	32
Lid is held open by a stay			•	Early models of the smaller sizes			Retrofit Option	Retrofit Option
Acrylic not bonded into an alloy frame								
As the lid is lifted, it clicks through a series of positions at which the hatch will hold open								
Catch of blocks in corners of lower frame								
Large inside handles have red or grey locking buttons inside handle								
Hinge has a black metal strap								

extending a short				
way over the acrylic				

Superhatch

- Produced 1980 1987.
- Spares no longer available

Handles



Hinge



Trimline

- o Produced 1988-1999
- Red locking button in larger handles
- Fastenings inside lip
- Metal sliding stay
- Seals and handles available as spares.

Handles



Lower Frame



Sliding Stay



Lid Profile



Coastline

- o Produced 1991 1999
- Locking button in larger handles
- o Fastenings inside lip
- Friction lever
- Seals, friction lever and handles available as spares

Handles



Lower Frame



Friction Lever



Lid Profile



Ocean Hatch

- Produces 1991 now
- Locking button in larger handles
- Inverted "J" profile lower frame
- Friction lever
- High profile lid
- Full range of spares available

Handles

Flanged or Flat Base Lower Frame Friction Lever







Low Profile Hatch

- o Produced 1998 now
- Replaceable acrylic panel
- o Small handles bonded on
- Mark 1 and Mark 2
- Quote acrylic marking when ordering spares



Handles

Flanged Lower Frame

Optional Friction Lid Profile Stay Kit available

Mark 1...

Mark 2...



Medium Profile Hatch

- Produced 1999 now
- Replaceable acrylic panel
- Mark 1 and Mark 2 -



Flanged Lower



Friction Lever



Lid Profile

Mark 1 & 2

Same as Low Profile

Optional Friction Stay Kit available

Handles

Frame



